



KINTEK SOLUTION

Homogenizer カタログ

Contact us for more catalogs of [Sample Preparation](#), [Thermal Equipment](#), [Lab Consumables & Materials](#), [Bio-Chem Equipment](#), 等

KINTEK SOLUTION

????

>>> ????????

KinTek Group Limited is one technology orientated organization, team members are devoted to probing the most efficient and reliable technology and innovations in the scientific researching equipment, fields like biochemical reacting, new materials researching, heat treatment, vacuum creating, refrigerating, as well as pharmaceutical and petroleum extracting equipment.



医薬品および化粧品用途向け 高せん断ホモジナイザー

商品番号: COA-7



前書き

当社の高速実験用乳化ホモジナイザーで実験室の効率を高め、正確で安定したサンプル処理を実現します。
医薬品・化粧品に最適です。

[詳細を学ぶ](#)

パラメータ	仕様
モデル	KT200-S
ディスプレイ	LEDデジタルチューブ
速度範囲	Φ12 & Φ18 ヘッド: 300 - 20,000 rpm
最大処理量 (H ₂ O)	300 ml
リフティング機構	手動
リフティングストローク	170 mm
モータータイプ	カーボンブラシモーター
電源	AC 220V / 50Hz
電力	220 W
正味重量	7.5 kg
寸法 (長さ×幅×高さ)	210 × 290 × 330 mm

パラメータ	仕様
モデル	KT-HET-25D
速度範囲	Φ25: 5,000 - 20,000 rpm (H ₂ O負荷時)
速度制御	無段階 (ノブ)
タイマー範囲	1 - 8 分
処理量 (H ₂ O)	Φ25: 7,000 ml
最大処理粘度	Φ25: 3,500 mPa·s
作業ヘッド寸法 (Φ×長さ)	Φ25 × 216 mm
作業ヘッド浸漬深さ	62 - 147 mm
作業ヘッド材質	SUS316L

パラメータ	仕様
電源	AC 220V 50Hz
電力	450 W
正味重量	9.54 kg
寸法 (長さ×幅×高さ)	320 × 220 × 630 mm

パラメータ	仕様
モデル	KT-HEA-36
速度範囲	Φ36: 8,000 - 24,000 rpm
速度制御	無段階 (6段階ダイヤル)
処理量範囲 (H ₂ O)	Φ36: 500 - 8,000 ml
最大処理粘度	Φ36: 10,000 mPa·s
作業ヘッド寸法 (Φ×長さ)	Φ36 × 225 mm
作業ヘッド浸漬深さ	150 mm
作業ヘッド材質	316 ステンレス鋼
電源	AC 160 - 250V 50Hz
電力	1,300 W
正味重量	7.85 kg
寸法 (長さ×幅×高さ)	315 × 200 × 670 mm

パラメータ	仕様
モデル	KT-HET-25DT
速度制御	無段階 (ノブ)
処理量 (H ₂ O)	Φ25: 7,000 ml
最大処理粘度	Φ25: 3,500 mPa·s
作業ヘッド寸法 (Φ×長さ)	Φ25 × 216 mm
作業ヘッド浸漬深さ	62 - 147 mm
作業ヘッド材質	SUS316L
温度測定範囲	-10 ~ 200°C
電源	AC 220V 50Hz
電力	1,050 W
正味重量	10.5 kg
寸法 (長さ×幅×高さ)	360 × 380 × 638 mm

製薬、化粧品、食品の研究開発向け高性能ラボ用ホモジナイザー

商品番号: KT-VHE



前書き

製薬、化粧品、食品向けのラボ用真空乳化ホモジナイザー。高せん断混合、真空脱気、スケールアップ可能な1L~10L。今すぐ専門家のアドバイスを入手！

[詳細を学ぶ](#)

パラメータ	KT-VHE-1	KT-VHE-2	KT-VHE-5	KT-VHE-10
撹拌容量	100-1000ml	100-2000ml	500-5000ml	1000-10000ml
撹拌速度範囲	0-230rpm	0-230rpm	0-230rpm	0-230rpm
撹拌パドルスタイル	SUS316Lアンカータイプ、PTFEウォールスクレーパー付き			
処理粘度	100000CP	100000CP	100000CP	150000CP
撹拌電力	120W	150W	150W	300W
乳化容量	500-1000ml	600-2000ml	2500-5000ml	5000-10000ml
ホモジナイズ速度範囲	8000-28000rpm	8000-28000rpm	8000-30000rpm	8000-30000rpm
ホモジナイザーヘッドモデル	20DG	25DG	25DG	25DG
ホモジナイザー電力	1300W	1300W	1300W	1300W
リアクター蓋ポート	撹拌、真空、ホモジナイザー、供給、温度プローブ+予備ポート3つ			
リフティングストローク	300mm	300mm	500mm	500mm
最大使用温度	120°C	120°C	120°C	120°C
達成可能な真空度	-0.098MPa	-0.098MPa	-0.098MPa	-0.098MPa
電源	AC220V 50Hz	AC220V 50Hz	AC220V 50Hz	AC220V 50Hz
正味重量	35kg	40kg	50kg	55kg
寸法（長さ×幅×高さ）	400×650×1100 mm	400×650×1100 mm	600×450×1100 mm	600×480×1200 mm

パラメータ	KT-VHE-1S	KT-VHE-2S	KT-VHE-5S	KT-VHE-10S
撹拌容量	100-1000ml	100-2000ml	500-5000ml	1000-10000ml
撹拌速度範囲	0-230rpm	0-230rpm	0-230rpm	0-230rpm
撹拌パドルスタイル	SUS316Lアンカータイプ、PTFEウォールスクレーパー付き			
処理粘度	100000CP	100000CP	100000CP	150000CP

パラメータ	KT-VHE-1S	KT-VHE-2S	KT-VHE-5S	KT-VHE-10S
攪拌電力	120W	150W	150W	300W
乳化容量	500-1000ml	600-2000ml	2500-5000ml	5000-10000ml
ホモジナイズ速度範囲	8000-28000rpm	8000-28000rpm	8000-30000rpm	8000-30000rpm
ホモジナイザーヘッドモデル	20DG	25DG	25DG	25DG
ホモジナイザー電力	1300W	1300W	1300W	1300W
リアクター材質	316Lステンレス鋼			
リアクター蓋ポート	攪拌、真空、ホモジナイザー、供給、温度プローブ + 予備ポート3つ			
リフティングストローク	300mm	300mm	500mm	500mm
最大使用温度	120°C	120°C	120°C	120°C
達成可能な真空度	-0.098MPa	-0.098MPa	-0.098MPa	-0.098MPa
電源	AC220V 50Hz	AC220V 50Hz	AC220V 50Hz	AC220V 50Hz
正味重量	35kg	40kg	50kg	55kg
寸法（長さ×幅×高さ）	400×650×1100 mm	400×650×1100 mm	600×450×1100 mm	600×480×1200 mm



Kintek Solution

Head Quarter: No.89 Science Avenue, High-Tech Zone,
Zhengzhou, China

