

# Uv Lamp Trolley

Item Number: KT-P05



## Introduction

The UV lamp trolley is made of cold-rolled plate sprayed with plastic, and adopts a double-lamp structure; it is movable, foldable, and equipped with universal wheels, which is very convenient to use.

[Learn More](#)

|                           |                        |        |         |         |
|---------------------------|------------------------|--------|---------|---------|
| Model                     | KT-C-I                 | KT-B-I | KT-C-II | KT-B-II |
| Voltage                   | AC220V 50Hz            |        |         |         |
| Input power               | 70VA                   |        | 130VA   |         |
| Number of tubes           | 2x30W                  |        | 4x30W   |         |
| Timing range              | 0-120min               |        |         |         |
| UV wavelength             | 253.7nm                |        |         |         |
| Irradiation intensity     | ≥90μ w/cm <sup>2</sup> |        |         |         |
| Lamp arm adjustment angle | 90°□120°□150°          |        |         |         |
| Outer packing size (mm)   | 1160x410x370           |        |         |         |
| Weight                    | 18kg                   |        | 24kg    |         |