

振動ディスクミル 小型実験用粉砕機

商品番号: KT-JZ



前書き

効率的な実験室粉砕のための多用途振動ディスクミルをご覧ください。地質学、冶金学、生物学などに最適です。今すぐ探索しましょう！

詳細を学ぶ

シリアル番号	モデル	供給サイズ (mm)	排出サイズ (メッシュ)	積載量 (g)	数量	電圧 (V)	モーター出力 (kW)	寸法 (長さx幅x高さ, mm)	重量 (kg)
1	JZGJ-50-1		80-300	50	1	220	0.18	300x300x400	45
2	JZGJ-50-1D		80-300	80-300	1	220	0.18	300x300x400	45
3	JZGJ-80-1		80-300	80	1	220	0.25	380x380x600	65
4	JZGJ-80-1D		80-300	80	1	220	0.25	380x380x600	65
5	JZGJ-80-2		80-300	80x2	2	220	0.25	380x380x600	80
6	JZGJ-80-2D		80-300	80x2	2	220	0.25	380x380x600	80
7	JZGJ-100-1		80-300	100	1	380	1.1	540x520x780	130
8	JZGJ-100-1D		80-300	100	1	380	1.1	540x520x780	130
9	JZGJ-100-2		80-300	100x2	2	380	1.1	540x520x780	160
10	JZGJ-100-2D		80-300	100x2	2	380	1.1	540x520x780	160
11	JZGJ-100-3		80-300	100x3	3	380	1.5	550x600x850	200
12	JZGJ-100-3D		80-300	100x3	3	380	1.5	550x600x850	200
13	JZGJ-100-4		80-300	100x4	4	380	2.2	600x550x850	210
14	JZGJ-100-4D		80-300	100x4	4	380	2.2	600x550x850	210
15	JZGJ-100-6		80-300	100x6	6	380	2.2	700x650x900	250
16	JZGJ-100-6D		80-300	100x6	6	380	2.2	700x650x900	250
17	JZGJ-100-7		80-300	100x7	7	380	2.2	700x650x900	260
18	JZGJ-100-7D		80-300	100x7	7	380	2.2	700x650x900	260
19	JZGJ-200-1		80-300	200	1	380	1.5	540x520x780	180
20	JZGJ-200-1D		80-300	200	1	380	1.5	540x520x780	180
21	JZGJ-200-2		80-300	200x2	2	380	1.5	550x600x850	210
22	JZGJ-200-2D		80-300	200x2	2	380	1.5	550x600x850	210

シリアル番号	モデル	供給サイズ (mm)	排出サイズ (メッシュ)	積載量 (g)	数量	電圧 (V)	モーター出力 (kW)	寸法 (長さx幅x高さ, mm)	重量 (kg)
23	JZGJ-200-3		80-300	200x3	3	380	2.2	700x650x900	220
24	JZGJ-200-3D		80-300	200x3	3	380	2.2	700x650x900	220
25	JZGJ-400-1		80-300	400	1	380	1.5	600x550x850	190
26	JZGJ-400-1D		80-300	400	1	380	1.5	600x550x850	190
27	JZGJ-1000-1D		80-300	1000	1	380	2.2	700x650x900	260
28	JZGJ-100-1DB		80-300	100	1	380	1.1	700x520x800	170
29	JZGJ-100-2DB		80-300	100x2	2	380	1.1	700x520x800	180
30	JZGJ-100-3DB		80-300	100x3	3	380	2.2	1000x580x900	210
31	JZGJ-100-4DB		80-300	100x4	4	380	2.2	1000x580x900	240
32	JZGJ-200-1DB		80-300	200	1	380	1.5	700x520x800	190