

## 振動ディスクミル小型ラボ用粉砕機

商品番号: KT-JZ



### 前書き

効率的な実験室用粉砕機、振動ディスクミルをご覧ください。地質学、冶金学、生物学などに最適です。今すぐご覧ください！

[詳細を学ぶ](#)

シリアル番号	モデル	フィード (mm)	排出量 (mesh)	投入量 (g)	数量	電圧 (V)	ポット電圧 (kW)	寸法 (LxWxH, mm)	重量 (kg)
1	JZGJ-50-1		80-300	50	1	220	0.18	300x300x400	45
2	JZGJ-50-1D		80-300	80-300	1	220	0.18	300x300x400	45
3	JZGJ-80-1		80-300	80	1	220	0.25	380x380x600	65
4	JZGJ-80-1D		80-300	80	1	220	0.25	380x380x600	65
5	JZGJ-80-2		80-300	80x2	2	220	0.25	380x380x600	80
6	JZGJ-80-2D		80-300	80x2	2	220	0.25	380x380x600	80
7	JZGJ-100-1		80-300	100	1	380	1.1	540x520x780	130
8	JZGJ-100-1D		80-300	100	1	380	1.1	540x520x780	130
9	JZGJ-100-2		80-300	100x2	2	380	1.1	540x520x780	160
10	JZGJ-100-2D		80-300	100x2	2	380	1.1	540x520x780	160
11	JZGJ-100-3		80-300	100x3	3	380	1.5	550x600x850	200
12	JZGJ-100-3D		80-300	100x3	3	380	1.5	550x600x850	200
13	JZGJ-100-4		80-300	100x4	4	380	2.2	600x550x850	210
14	JZGJ-100-4D		80-300	100x4	4	380	2.2	600x550x850	210
15	JZGJ-100-6		80-300	100x6	6	380	2.2	700x650x900	250
16	JZGJ-100-6D		80-300	100x6	6	380	2.2	700x650x900	250
17	JZGJ-100-7		80-300	100x7	7	380	2.2	700x650x900	260
18	JZGJ-100-7D		80-300	100x7	7	380	2.2	700x650x900	260
19	JZGJ-200-1		80-300	200	1	380	1.5	540x520x780	180
20	JZGJ-200-1D		80-300	200	1	380	1.5	540x520x780	180
21	JZGJ-200-2		80-300	200x2	2	380	1.5	550x600x850	210
22	JZGJ-200-2D		80-300	200x2	2	380	1.5	550x600x850	210

シリアル番号	モデル	フィード (mm)	排出量 (mesh)	投入量 (g)	数量	電圧 (V)	ポット電圧 (kW)	寸法 (LxWxH, mm)	重量 (kg)
23	JZGJ-200-3		80-300	200x3	3	380	2.2	700x650x900	220
24	JZGJ-200-3D		80-300	200x3	3	380	2.2	700x650x900	220
25	JZGJ-400-1		80-300	400	1	380	1.5	600x550x850	190
26	JZGJ-400-1D		80-300	400	1	380	1.5	600x550x850	190
27	JZGJ-1000-1D		80-300	1000	1	380	2.2	700x650x900	260
28	JZGJ-100-1DB		80-300	100	1	380	1.1	700x520x800	170
29	JZGJ-100-2DB		80-300	100x2	2	380	1.1	700x520x800	180
30	JZGJ-100-3DB		80-300	100x3	3	380	2.2	1000x580x900	210
31	JZGJ-100-4DB		80-300	100x4	4	380	2.2	1000x580x900	240
32	JZGJ-200-1DB		80-300	200	1	380	1.5	700x520x800	190